

PRODUCT DATASHEET

Floating Lantern **EVEREADY**

5109

WEATHERPROOF

- Meets IEC 60529 IPX4 requirements
- Survives rough weather on the job



FLOATS

- Floats for easy recovery from water



BRIGHT

- Provides 35 lumens
- Large reflector for broader beam



DURABLE

- Shatterproof lens
- Rugged polyethylene body
- Survives 1 meter drop



AMERICAN MADE

- Great for contracts requiring "Buy American"



A great choice for wet areas and outdoor work, the 5109 is weatherproof and floats for easy recovery from water. It stays where you put it and provides a large lit area, making it a terrific area light.

A shatterproof lens and a rugged polyethylene case help it stand up to rough job site conditions. Made in the USA, it is an ideal light for municipal contracts requiring Buy American.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Eveready Floating Lantern
Model:	5109
Color:	Yellow
Power Source:	One 6V Spring Terminal Lantern Battery
ANSI / NEDA:	Series 908D or 908A
Lamp:	PR-13
Lamp Life (hr):	15 Hours
Lamp Output (lumens):	35
Lamp Rating:	4.75V, 0.5A
Beam Distance (m):	270
Peak Beam Intensity (cd):	18,200
Run Time (h:mm):	13
Typical Weight:	220 grams (7.7 oz.) (without battery)
Dimensions (mm):	117 x 183 x 99

Performance:



Tested according to ANSI / NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
 ©Energizer / All Rights Reserved