


8 7 6 5 4 3 2 1



STANDARD SERIES

SCREW - STAINLESS STEEL
HOUSING - ZINK, NICKEL PLATED
SOLDER TERMINAL- BRASS, ELECTROTIN PLATED
INSULATOR - POLYESTER, GREEN (UL94V-0)
CONTACT PIN - BRASS, SILVER PLATED

C - M

CONTACT PLATING
BLANK = SILVER (STANDARD)
AU = GOLD

HOUSING FINISH
BLANK = NICKEL PLATE (STANDARD)
B = BLACK

NO. OF CONTACTS:
3 = 3 CONTACTS
4 = 4 CONTACTS
5 = 5 CONTACTS
6 = 6 CONTACTS
7 = 7 CONTACTS


PROFESSIONAL SERIES

SAME AS ABOVE EXCEPT
CONTACT PIN - PHOSPHOR BRONZE, GOLD OVER NICKEL




QGP - 27

NO. OF CONTACTS:
3 = 3 CONTACTS
4 = 4 CONTACTS
5 = 5 CONTACTS
6 = 6 CONTACTS
7 = 7 CONTACTS

NOTE:
1. ALL DIMENSIONS ARE REFERENCE, UNLESS OTHERWISE SPECIFIED.



RECOMMENDED
PANEL CUT-OUT



CUSTOMER DRAWING

G	21136	2-3-97	MM	RB	★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
F	21070	2-3-97	MM	RB		SIZE	WIDTH	MULT	LBS/M	TEMPER
E	21035	2-3-97	MM	RB		FINISH			MATERIAL	
D	20627	1-20-96	SG	SG		SPEC No.			SPEC No.	
C	20534	12-9-95	SG	RB		FIRST USED ON		SCALE 2:1		Switchcraft® SHEET OF
						DATE DRAWN	BY	CHKD	APVD	
H	22838	9-30-99	JL	DG		8-10-94	SG	SG 8-10-94	GHJ 8-10-94	
REV	ECO NUMBER	DATE	BY	APVD	NAME			PART No.		REV
REVISIONS					C SERIES MALE QG			C_M SERIES		H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[C7M](#)