


**Part Number: 500027-2041**

**0.40mm Pitch Board-to-Board SlimStack™ Plug, Surface Mount, Dual Row, Vertical, 0.95mm Mated Height, with Friction Lock, Lead-Free, 20 Circuits, Reel Size Diameter 330.00mm, Reel Quantity 2,000**



Series image - Reference only

|                  |   |
|------------------|---|
| <b>Status:</b>   | Contact Molex   |
| <b>Series:</b>   | 500027  |
| <b>Category:</b> | PCB Headers   |
| <b>Overview:</b> | <a href="#">SlimStack™ 0.40mm Pitch Board-to-Board Connectors</a> |

**Mates With Part(s):**

[500024](#) SlimStack™ Board-to-Board Receptacle

**Product Environmental Compliance**

**EU RoHS:** ELV and RoHS Compliant

**China RoHS:** 

**REACH SVHC:** Contains SVHC: No

**Low-Halogen Status:** Low-Halogen

**Part Detail****General**

|               |   |
|---------------|---|
| <b>Status</b> | <b>Contact Molex</b>  |
| Category      | PCB Headers   |
| Series        | <a href="#">500027</a>  |
| Application   | Board-to-Board, Signal  |
| Comments      | Solder Tab Plating: Lead-Free, Tin                                |
| Overview      | <a href="#">SlimStack™ 0.40mm Pitch Board-to-Board Connectors</a> |
| Product Name  | SlimStack™  |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | No                             |
| Circuits (Loaded)              | 20                             |
| Circuits (maximum)             | 20                             |
| Color - Resin                  | Natural                        |
| Durability (mating cycles max) | 10                             |
| First Mate / Last Break        | No                             |
| Glow-Wire Compliant            | No                             |
| Guide to Mating Part           | Yes                            |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | Yes                            |
| Mated Height                   | 0.95mm                         |
| Material - Metal               | Phosphor Bronze                |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Gold                           |
| Material - Resin               | High Temperature Thermoplastic |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 0.47mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | Yes                            |
| Packaging Type                 | Embossed Tape on Reel          |
| Pitch - Mating Interface       | 0.40mm                         |
| Pitch - Termination Interface  | 0.40mm                         |
| Plating min - Mating           | 0.102µm                        |
| Plating min - Termination      | 0.035µm                        |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | Partial                        |
| Stackable                      | No                             |
| Temperature Range - Operating  | -25°C to +85°C                 |
| Termination Interface: Style   | Surface Mount                  |

**Electrical**

**(Please review the Product Specification for specific details.)**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.1A |
| Voltage - Maximum             | 50V  |

**Material Info**

|     |              |
|-----|--------------|
| UPC | 822348804221 |
|-----|--------------|

**Reference - Drawing Numbers**

|                       |   |
|-----------------------|---|
| Product Specification | PS-500024-011, RPS-500024-019, RPS-500024-025, RPS-500024-030, RPS-500024-031, RPS- |
|-----------------------|---|

|               |  |
|---------------|--|
|               | 500024-032, RPS-500024-034, RPS-500024-038, RPS-500024-039, RPS-500024-040, RPS-500024-041 |
| Sales Drawing | SD-500027-028, SD-500027-029   |

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)