


USED ON	
---------	--



Left Side
Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Slate
Geom. Spec: N/A

Fiber Path

A - _____ - B
B - _____ - A

Right Side
Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

- Notes:
- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 2 Includes dust caps (not shown on print).
 - 3 IL tested at 1300nm.
 - 4 Label 2 will not be present on any cable assembly less than 5 meters long.

A	Rev Per EC#	RELEASE	1/25/2008	-	JD
P	LTR	REVISION RECORD	DATE	DIN	APVD

DIMENSIONS:		0 1 2 3 4
meters		
		

TOLERANCES UNLESS OTHERWISE SPECIFIED:		
PLC	±	"
PLC	±	"
PLC	±	"
PLC	±	"
PLC	±	"

Restricted To:

DWT Cable Assy Configurator CHK Jeremy Duncan APVD Jeremy Duncan		MATERIAL -  Tyco Electronics, Inc. Harrisburg, PA 17105-3608	HEAT TREAT
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex		DRAWING NO C- 1906099	SHEET 1 of 4 REV A

OSOLET

REVISIONS

LOC	CE	DIST	16
Customer Layout 1			

APPLICABLE. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN THE ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	1/25/2008	-	JE
P	LTR	REVISION RECORD		DATE	DIN	AP

Qty	U of M	Description	Item No
2	piece	Trace Label	7
4	piece	Eyelet/Shrink tube assembly - White	6
AR	meter	2 Fiber, XG-50/125, 2.0mm, Twinzip, Aqua, OFNR (Riser)	5
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	4
2	piece	LC Connector Assy, MM	3
2	piece	LC Duplex clip, black	2
4	piece	LC. SC. FC Straight Boot. Beige	1

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK Jeremy Duncan	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
		1 P/LC - - 2 P/LC - - 3 P/LC - - 4 P/LC - -		APD Jeremy Duncan			
		NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex					SHEET 2 of 4
Restricted To:					NTS A2	DRAWING NO C- 1906099	REV A

Restricted To:

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Slate		LC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1906099-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1906099-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1906099-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1906099-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1906099-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1906099-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1906099-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1906099-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
5-1906099-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1906099-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1906099-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1906099-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1906099-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1906099-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1906099-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1906099-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1906099-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1906099-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1906099-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1906099-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1906099-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1906099-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1906099-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1906099-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1906099-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1906099-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1906099-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1906099-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1906099-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1906099-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1906099-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1906099-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1906099-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1906099-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1906099-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1906099-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1906099-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1906099-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

	A	Rev Per EC#	RELEASE	1/25/2008	-	JC			
P	LTR	REVISION RECORD			DATE	DIN	AP		

DIMENSIONS; meters	
	

Restricted To:

DATA Cable Assy Configurator CHK Jeremy Duncan APVD Jeremy Duncan		MATERIAL -  Tyco Electronics, Inc. Harrisburg, PA 17105-3608	HEAT TREAT -
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex			
SCALE NTS	SIZE A2	DRAWING NO. C-1906099 SHEET 3 of 4	REV A

D

C

B

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8 7 6 5 4 3 2 1

	A	Rev Per EC#	RELEASE	1/25/2008	-	JD	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ±
1 P.L.C. ±
2 P.L.C. ±
3 P.L.C. ±
4 P.L.C. ±

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Jeremy Duncan			
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906099	SHEET 4 of 4	REV A

Label 1

Per specification 107-1645-1

Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1

Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

Part Number

Country of Origin

This label is used on all lengths on this drawing.

D
C
B
A