

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010181090

Status:

Active

Description:

2.36mm (.093") Diameter Standard .093" Pin and Socket Header, Shrouded, 9 Circuits, 9 Male Terminals

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Product Name

PCB Headers

3099

Wire-to-Board

Solder Type|Round Pin

Standard .093"

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Lock to Mating Part

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

9

9

Black

25

94V-2

No

Yes

Tin

Tin

Polyester

3

Vertical

0.170 In

4.32 mm

Yes

None

0.062 In

1.60 mm

Bag

0.198 In

5.03 mm

Yes

Fully

No

No

-40°C to +105°C

Through Hole

Electrical

CSA

Current - Maximum

UL

Voltage - Maximum

LR19980

5A

E29179

250V

Material Info

Old Part Number

A30990901

Reference - Drawing Numbers

Sales Drawing

SDA-3099-09**




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3099Series

Mates With

03-09-1091 , 03-09-1094

This document was generated on 01/15/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION