





















Hot air nozzles for HAP 1 WMD 3K, WMD 1A, WAD 101, WMA 3V

	Model	Dimensions	Components	Description	Order No.
Round nozzles					
	F06	12,0 x 1,5 mm		flat nozzle	005 87 277 72
	F04	10,5 x 1,5 mm		flat nozzle	005 87 277 73
	F02	8,0 x 1,5 mm		flat nozzle	005 87 277 74
	R10	Δ 2,0 mm		round nozzle	005 87 277 87
	R08	Δ 2,0 mm		round nozzle, bent	005 87 277 86
	R06	Δ 3,0 mm		round nozzle	005 87 278 22
	R04	Δ 1,2 mm		round nozzle	005 87 278 21
	R02	Δ 0,8 mm		round nozzle	005 87 278 23
	FD4	Δ 1,5 x 10,0 mm		dual nozzle	005 87 277 75
	FD2	Δ 1,5 x 8,0 mm		dual nozzle	005 87 277 76

100 W



	Model	Dimensions X x Y	Components	Description	Order No.
Two sides heated (type D)					
	D10	18,0 x 10,0 mm	SO 28	hot air nozzle with hotplate	005 87 277 84
	D08	15,0 x 10,0 mm		hot air nozzle with hotplate	005 87 277 81
	D06	13,0 x 10,0 mm		hot air nozzle with hotplate	005 87 277 82
	D04	10,5 x 10,5 mm		hot air nozzle with hotplate	005 87 277 79
All 4 sides heated (type D)					
	SK 709 SK 769A Q10	12,0 x 12,0 mm 16,0 x 16,0 mm 18,0 x 18,0 mm		hot air nozzle with hotplate	005 87 278 12 005 87 278 16 005 87 277 85
	Q08	12,5 x 15,0 mm		hot air nozzle with hotplate	005 87 277 83
	Q06	15,0 x 10,0 mm		hot air nozzle	005 87 277 80
	Q04	6,0 x 9,0 mm		hot air nozzle	005 87 277 78
	Q02	6,0 x 6,5 mm		hot air nozzle	005 87 277 77
Measuring nozzle					
	R01			measuring nozzle	005 87 278 08