


# INTERFACE MODULES & SUPPORTS

## RJ45 Interface Module

- Single RJ45 (8P8C) type socket to screw terminals
- Terminals marked 1 to 8 (+ Shield)
- Separate shield connection
- 35mm DIN rail mounting
- Option for 32mm (G) rail mounting
- Available with optional wall mounting plates
- 45° terminals for easy access
- RoHS compliant
- SVHC free (2012)

CIM/RJ45



| SPECIFICATION       |                                  |              |              |
|---------------------|----------------------------------|--------------|--------------|
| Rating              | 125V DC 500mA                    |              |              |
| Cable entry         | 0.2-4mm <sup>2</sup> (30-12 AWG) |              |              |
| Terminal screw      | M3                               |              |              |
| Strip length        | 6mm (0.24")                      |              |              |
| Max terminal torque | 0.5Nm (4lb-in)                   |              |              |
| Dimensions:         | Height:                          | Width:       | Length:      |
|                     | 45mm (1.77")                     | 83mm (3.27") | 34mm (1.02") |

| TYPE NO. | DESCRIPTION                                               |
|----------|-----------------------------------------------------------|
| CIM/RJ45 | RJ45 to screw terminal interface. 35 mm din rail mounting |

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

ENCLOSURES

BATTERIES

TRANS-  
FORMERS



+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com

We operate a constant improvement policy,  
our products are subject to change without notice.

