



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			K2	REVISED PER ECO-11-004917	11MAR11	RK HMR



- 1 FOR 1.27[.050] TO 2.08[.082] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK 0.46 ± 0.05[.018 ± .002]
- 3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

-	100	LOOSE PC, BOX	BODY: COPPER ASTM-B152 TIN PL ASTM-B545 SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545 INSULATION: NYLON ASTM-D4066 COLOR: YELLOW, TYPE I	8-323915-1
-	4000	ON TAPE, REEL		2-323915-2
2-323915-2	1	WIRE TERMINAL		323915
PART NO ON TAPE	QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 18MAR10		 TE Connectivity							
		CHK JEFF RUTH 18MAR10									
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.20[.008] 4 PLC ± - ANGLES ± 0° 30'	APVD TOM MICHIELUTTI 18MAR10		NAME WIRE TERMINAL PIDG – RING TONGUE WIRE SIZE: 26–22							
		PRODUCT SPEC —									
MATERIAL SEE TABLE		APPLICATION SPEC —					SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
		WEIGHT —					A3	00779	C-323915		—
		FINISH SEE TABLE	CUSTOMER DRAWING		SCALE	12:1	SHEET	1 of 1	REV	K2	