


[> PN Search](#)
**YA28L3**
[> Electrical Power Interconnect division](#)
FCI brings you more
[✉ Contact our sales/technical support](#)
[✉ Sample request](#)
[€ Price request](#)
[📊 Check distributor stock](#)
[📄 Download](#)
[📏 Mating half](#)
[📦 Alternative parts](#)
[🔧 Application tooling](#)

Not Applicable

Not Available

[Electrical Tooling](#)
[Installation Tooling](#)

Features Selected

Region	US
Wire Type	Commercial Stranded Copper
Wire Size	4/0 AWG
Stud Hole Size	5/16 in.
Stud Hole Spacing	One Hole
Barrel Length	Standard
Tongue Angle	Straight
Tongue Width	1.02 in.

Other Properties

Element A Index	15
UL Listed	yes
CSA Certified	yes
Strip Length	1-1/8 in.

[Home page](#)

Product quick search

P/N Search

Product type search

[Alphabetical list](#)
[Connection type](#)
[Markets / Applications](#)
[Product finder](#)
[Literature](#)
[Services](#)
[Contact us](#)
[Registered users](#)
[Forgot password ?](#)
[Register now](#)