

List Price \$234.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Horsepower Rating (1-Phase)	3HP@115Vac - 7.5HP@230Vac
Contactor Type	Non-Reversing
Inductive Amperes (AC3)	50A
Resistive Amperes (AC1)	80A
Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Maximum Voltage Rating	600 Vac
Marketing Trade Name	TeSys
Horsepower Rating (3-Phase)	15HP@200/230Vac - 40HP@460/575Vac
Number of Poles	3-Pole (3 NO)
Coil Voltage	120Vac@50/60Hz
Mounting Style	35mm DIN Rail
Coil Consumption Sealed	13 VA
Coil Voltage Code	G7
Coil Consumption Inrush	140 VA
Terminal Type	Screw Clamp
Weight	0.855 lbs (0.388 kg)
Power Terminal Torque	70 lb-in (8 Nm)
Type	TeSys D
Control Wire Size	#12 to #20 AWG
Power Wire Size	#2 to #16 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901934622
Package Quantity	1
Weight	2.07 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	ID

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.