



5-Pole, Male

DeviceNet, 5-pole, male field attachable 7/8" connector with screw terminal connection, cable outlet suitable for THIN and THICK DeviceNet cable.



5-Pole, Female


DeviceNet, 5-pole, female field attachable 7/8" connector with screw terminal connection, cable outlet suitable for THIN and THICK DeviceNet cable.



Pin Assignments

Face Views / 7/8"

5 pole





Be Certain with Belden

DeviceNet Field Attachable Connectors, M12

0936 DMC 301 | 0936 DMC 303 | 0936 DFC 301 | 0936 DFC 303

Technical Data

Environmental	
Degree of protection	IP 67 / NEMA 6P
Operating temperature range	-40°C (-40°F) / +90°C (+194°F)

Materials	
Housing / Molded body	PA
Insert	TPU, self-extinguishing
Contact	CuZn, pre-nickel and 0.8 microns gold-plated
Coupling nunt	Aluminum, black anodized
O-ring	NBR

Mechanical	
Mode of connection	Screw terminals
Connectable conductor	max. 1.5 mm²

Electrical	
Current rating	8 A
Voltage rating	250 V

Part Number		Pins	Cable Type	Characteristics
0936 DMC 301		5	Thin	 
0936 DMC 303		5	Thick	 
	0936 DFC 301	5	Thin	 
	0936 DFC 303	5	Thick	 