


### Application and Features

- Standard: tube packing and without "locating pegs"
- Assures reliable PC Board connections
- Fine pitch, high profile type with 0.30mm square pin
- Mate with female header on page 6 then "board to board" distance 4.25 mm

### PCB Surface Mount Layout



### SPECIFICATIONS

Current rating	1 A
Insulator resistance	5000 MΩ min.
Contact resistance	20 mΩ max.
Dielectric withstanding	AC 500 V

Operating temperature	- 40°C to + 105°C
Processing temperature	+ 230°C for 30 sec. max.
	+ 260°C for 10 sec. max.
Contact material	Copper alloy
Insulator material	LCP UL 94 V-0

### How to order

SLS - xxx - H 720 - 11/00 X

Nbr of contacts	Plating	Packing and "pick & place pad" Option
<b>006 to 060</b>	<b>11</b> = gold other platings on request	<b>without "locating pegs"</b> <b>A</b> = tube packing and pick & place pad <b>B</b> = tape & reel packing and pick & place pad
		<b>with "locating pegs"</b> <b>C</b> = locating pegs and tube packing <b>D</b> = locating pegs; tube packing; pick & place pad <b>E</b> = locating pegs; tape & reel packing; pick & place pad