

High Accuracy, Low Profile, 2 Wire Temperature Transmitter



2 Wire Low Profile Temperature Transmitters

The 300TX is a 4-20mA analogue temperature transmitter, which can be housed, in a probe terminal head suitable for a DIN standard block. **The overall height is only 23mm allowing it also to be housed in low-profile enclosures.** With ranges for thermocouple and Pt100 sensors, the units offer an exceptionally wide range of span adjustment, which reduces the need for stockholding different temperature ranges. A novel feature is the minimal-interaction span and zero potentiometer action, which is time saving and convenient when calibrating, or re-scaling.

- 4-20mA, 2 wire loop
- High accuracy & stability
- In-head mounting, DIN standard fixing
- Pt100 or thermocouples type J and K
- Effective input 'noise' rejection
- CE compliant
- RoHS compliant

Specification

Ranges	Thermocouple to IEC 584	Type J	0-300°C
		Type K	0-1100°C
		Type K	0-200°C
PT100 to IEC751, 3 wire			
			0 to 200°C
			0 to 100°C

Junctions/ sensors must be insulated from sheath

Output 4-20mA loop powered, max 30mA. Directly proportional to mV input for thermocouples. Directly proportional to temperature for Pt100.

Loop supply 12-36V dc; reverse connection protected.

Accuracy Thermocouple ranges $\pm 0.2\%$ of span (linear to mV input)
Pt100 ranges $\pm 0.1\%$ of span (linear to temperature input)

Range	Farnell Code	Labfacility Stock Code
Pt100, 0-100 degC	163-3463	SI-060
Pt100, 0-200 degC	163-3464	SI-061
Type J, 0-300 degC	163-3465	SI-062
Type K, 0-200 degC	163-3467	SI-063
Type K, 0-1100 degC	163-3468	SI-064

Data Ref; FAR77