

PERFORMANCE DETAIL

Insert 1P.M08 : 8 Low Voltage

Insulator

Specifications

Contact Type: Print (straight)

Max. Matings: 2000

Contact Dia.: 0.7 mm (0.0275in)

R (max): 6.5 mOhm



OTHER CHARACTERISTICS

F ret (min): 50 N

F ret (max): 150 N

IP Rating 50



Related links



Contact



Quote Request



Catalogs Downloads



Catalogs Requests



Sample Request



3D drawings



[P_series_catalog.pdf](#)