



Accessories

G-79

| More Information | |
|-----------------------------------------------------------------------------------|----------------------------|
|  | Spec Sheet |
|  | RoHS Compliant |

Specifications

Revision: 1.16

P/N 61663;Black Neoprene Gasket for 07/09 bodies (AudioLarm, Ultra, OneTouch, Announcer)

Operating Mode:

Operating Voltage:

Operating Temperature: -20_C to +65_C

Storage Temperature: -40_C to +85_C

Surge Voltage: 20% over maximum rated voltage for less than 5 minutes

Reverse Voltage Protection: To the maximum operating voltage

Construction Materials: 60 Durometer Neoprene

Environmental Durability: ASTM B117 Certified - Withstands exposure to salt spray for 300 hours
IP 68 Certified - Withstands water submergence and dust exposure
Humidity- 95% relative humidity at +40_C continuously for 100 hours.
Vibration- Withstands vibration between 0 and 55 Hz. on all axes.

Life Expectancy: 10 years under normal operating conditions.

Warranty: For a period of two years from the date of manufacture under normal operating conditions.