



BIT,NAILEATER 7/8(.875)X 7.54(61PTS-7/8)

Nail Eater Extreme

Cat No: 61PTS-7/8

UPC No: 783310304272

Description

- "Improved cutting edge provides 30% longer life span
- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Unique patented design cutting angle - smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel
- cuts through nails and provides longer life
- "Shorty" bits - for working in tight places, yet still can go through three abutting 2 x 4s
- See "Bit Extensions" if more length is required
- P.O.P packaged "

Specifications

- Bit Diameter : 7/8 IN (22.200 MM)
- Electric Drill Required : 61 PTS - 5/8 Through 61 PTS -1, Minimum 3/8 IN Drill, All Big Shank, 1/2 IN Drill
- Material : Heat Treated Steel
- Overall Length : 7-5/8 IN (193.700 MM)
- Shank Diameter : 5/16 IN (7.900 MM)
- Shank Type : Hexagonal
- Sub Brand : Nail Eater
- Twist Length : 5.000 IN (127.000 MM)
- Type : Extreme Shorty
- Weight : 0.500 LB (227.000 GM)