


PIN RECEPTACLES

**FOR .015" - .020" DIAMETER PINS (#11 CONTACT)
AND .015" - .022" DIAMETER PINS (#21 CONTACT)
(SEE SPECIFIC CONTACT RANGE ON PAGE 251)**

0548

0548-0-15-XX-21-XX-10-0


Solder mount in .036 min. mounting hole



8975

8975-0-15-XX-21-XX-10-0


Solder mount in .036 min. mounting hole



3016

3016-0-15-XX-21-XX-10-0


Solder mount in .036 min. mounting hole



9548

9548-0-15-XX-21-XX-10-0


Solder mount in .036 min. mounting hole



8637

8637-0-15-XX-21-XX-10-0


Solder mount in .037 min. mounting hole



1407

1407-0-15-XX-11-XX-10-0


Solder mount in .040 min. mounting hole



0553/8553

X553-X-15-XX-X1-XX-10-0

Hex press-fit in .041 plated through-hole




Basic Part Number	Length L	Depth N
0553-1	.140	.124
0553-2	.170	.154
0553-3	.282	.266
8553-0	.245	.229

0566

0566-X-15-XX-21-XX-10-0

Solder mount in .039 min. mounting hole




Basic Part Number	Length L
0566-1	.083
0566-2	.138

0442

0442-0-15-XX-11-XX-10-0


Solder mount in .040 min. mounting hole



0554

0554-0-15-XX-21-XX-10-0

Solder mount in .040 min. mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 15 - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 100 μ " TIN/LEAD OVER NICKEL
- ◆ 84 100 μ " TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#11 or #21 CONTACT (DATA ON PAGE 251)

(For alternate contact choices, see group A on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[9548-0-15-01-21-02-10-0](#) [8975-0-15-01-21-27-10-0](#) [3016-0-15-01-21-02-10-0](#) [3016-0-15-01-21-27-10-0](#) [0553-2-15-80-11-27-10-0](#) [0553-1-15-80-21-27-10-0](#) [0552-2-15-80-21-84-10-0](#) [0552-2-15-80-21-27-10-0](#) [0552-2-15-80-11-84-10-0](#) [0552-2-15-80-11-27-10-0](#) [0552-1-15-80-11-27-10-0](#) [0552-1-15-15-11-27-10-0](#) [0552-2-15-15-11-27-10-0](#) [0548-0-15-15-11-27-10-0](#) [1407-0-15-15-11-27-10-0](#) [0553-1-15-15-11-27-10-0](#) [0553-2-15-15-11-27-10-0](#) [0554-0-15-15-11-27-10-0](#) [0553-2-15-01-21-27-10-0](#) [0553-1-15-01-11-27-10-0](#) [0553-3-15-01-11-27-10-0](#) [0553-2-15-01-11-27-10-0](#) [0566-2-15-15-21-27-10-0](#) [0566-1-15-15-21-27-10-0](#) [0552-2-15-01-11-27-10-0](#) [0552-1-15-01-11-27-10-0](#) [0548-0-15-01-11-27-10-0](#) [1407-0-15-01-11-27-10-0](#) [0569-0-15-01-11-14-10-0](#) [0553-3-15-15-11-27-10-0](#) [0569-0-15-01-11-27-10-0](#) [0552-2-15-15-21-27-10-0](#) [0554-0-15-01-11-27-10-0](#) [0553-2-15-15-21-27-10-0](#) [1407-0-15-01-11-02-10-0](#) [0566-2-15-01-21-02-10-0](#) [0566-2-15-01-21-27-10-0](#) [0566-1-15-01-21-02-10-0](#) [0566-1-15-01-21-27-10-0](#) [0554-0-15-01-21-02-10-0](#) [0554-0-15-01-21-27-10-0](#) [0553-3-15-01-21-02-10-0](#) [0553-3-15-01-21-27-10-0](#) [0553-3-15-01-11-02-10-0](#) [0553-2-15-01-21-02-10-0](#) [0553-2-15-01-11-02-10-0](#) [0553-1-15-01-21-02-10-0](#) [0553-1-15-01-21-27-10-0](#) [0553-1-15-01-11-02-10-0](#) [0552-2-15-01-21-02-10-0](#) [0552-2-15-01-21-27-10-0](#) [0552-2-15-01-11-02-10-0](#) [0548-0-15-01-21-02-10-0](#) [0548-0-15-01-21-27-10-0](#) [0442-0-15-01-11-02-10-0](#) [0442-0-15-01-11-27-10-0](#) [0442-0-15-15-11-27-10-0](#) [0548-0-15-15-21-27-10-0](#) [0552-1-15-15-21-27-10-0](#) [0553-1-15-15-21-27-10-0](#) [0553-3-15-15-21-27-10-0](#) [0554-0-15-15-21-27-10-0](#) [3016-0-15-15-21-27-10-0](#) [8637-0-15-15-21-27-10-0](#) [8975-0-15-15-21-27-10-0](#) [0553-3-15-00-21-00-10-0](#) [0569-0-15-00-21-00-10-0](#) [0553-2-15-00-21-00-10-0](#) [8553-0-15-00-11-00-10-0](#) [0552-2-15-00-21-00-10-0](#) [0553-2-15-00-00-00-10-0](#) [1407-0-15-00-00-00-10-0](#) [0554-0-15-00-00-00-10-0](#) [0553-1-15-00-21-00-10-0](#) [0548-0-15-00-00-00-10-0](#) [8553-0-15-00-21-00-10-0](#) [8637-0-15-00-00-00-10-0](#) [8975-0-15-00-00-00-10-0](#) [0552-1-15-00-21-00-10-0](#) [0553-3-15-00-00-00-10-0](#) [0566-2-15-00-00-00-10-0](#) [9548-0-15-00-00-00-10-0](#) [3016-0-15-00-00-00-10-0](#) [0566-1-15-80-21-14-10-0](#) [0552-1-15-01-11-14-10-0](#) [8637-0-15-15-21-14-10-0](#) [3016-0-15-01-21-14-10-0](#) [0553-3-15-01-21-14-10-0](#) [0553-1-15-01-21-14-10-0](#) [0553-2-15-80-11-14-10-0](#) [1407-0-15-80-11-14-10-0](#) [0553-3-15-80-11-14-10-0](#) [0569-0-15-80-11-14-10-0](#) [0566-2-15-80-21-14-10-0](#) [0552-1-15-80-21-14-10-0](#) [0553-3-15-80-21-14-10-0](#) [0552-2-15-80-21-14-10-0](#) [0553-2-15-80-21-14-10-0](#) [0552-1-15-80-11-14-10-0](#) [0553-1-15-80-21-14-10-0](#)