

GNM1M25C1H680KD01#

" # " indicates a package specification code.

Discontinued

General


125℃


Reflow OK

RoHS

< List of part numbers with package codes >
GNM1M25C1H680KD01D

Shape





L size	1.37 ± 0.15mm
W size	1.0 ± 0.15mm
T size	0.6 ± 0.1mm
Distance between external terminals P	0.64 ± 0.05mm
Size code in inch(mm)	0504 (1410)

References

Packaging	Specifications	Minimum quantity
D	180mm Paper taping	4000

Mass (typ.)	
1 piece	4.5mg
180mm Reel	136g

Specifications

Capacitance	68pF ± 10%
Rated voltage	50Vdc
Temperature characteristics (complied standard)	COG(EIA)
Temperature coefficient	0 ± 30ppm/
Temperature range of temperature characteristics	25 to 125
Operating temperature range	-55 to 125

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.