

Part Number

FGN.2M.319.XLCT



Size/Series 2MN / M

[Request a quote](#)

MECHANICAL DETAILS

Shell Style/Model	FG*: Straight plug with arctic grip and mold stop
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material	Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces bronze/brass
Cable Fixing	∅ : 0 - 0 mm
Variant	:

	A	B	C	D	F	I	L	M	P	X
mm.	18.9	14.0	17.2	13.0	15.5	1.5	30.5	10.1	4.0	7.1
in.	0.74	0.55	0.68	0.51	0.61	0.06	1.20	0.40	0.16	0.28



PERFORMANCE DETAILS

Insert Configuration Specifications	2M.319 : 19 Low Voltage
Contact Type:	Crimp
Max. Matings:	5000
Contact Retention:	22 N
Contact Dia.:	0.7 mm (0.028in)
Bucket Dia.:	0.8 mm (0.031in)
Min. Conductor:	0.14 mm ² (AWG 26)
Max. Conductor:	0.34 mm ² (AWG 22)
R (max):	6.1 mOhm
Test voltage (kV rms)	1.55
Contact-contact:	
Test voltage (kV rms)	0.95
Contact-shell:	
Rated current (A):	5

OTHER CHARACTERISTICS

Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Operating temperature:	-55°C/ +200°C
Climatical Category:	15/200/21 (Al. shell)
Lighting strike EIA 364-75	10K amps - 6 times
EMI Shielding EIA 364-66A	- 1Ghz-80 dB,3GHz-70 dB,6GHz- 58dB
IP Rating	68
Catalog	

[Download 3D draw](#)[Copyright](#) [Privacy policy](#) [Product safety](#)