

181-21006

Slotted Wall Wiring Duct, 2" X 1", Non-Adhesive, PVC, White, 30'/Box

Article Number: 181-21006

Part Number: 181-21006

Type: SL2X1

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[!\[\]\(3342c215b2a8b663596a81468d5dc314_img.jpg\)](#) [!\[\]\(5e22d44aef1f9548ca8274cbfb388e9d_img.jpg\)](#) [!\[\]\(b011182daf5a0527ed818f91dc4cf8f7_img.jpg\)](#) [!\[\]\(e021942709a217cfed2f781c62feb09c_img.jpg\)](#) | [!\[\]\(189fbc627457efb1015bb006253636f9_img.jpg\) Share](#)

[Base Data](#)

Part No.	181-21006
Type	SL2X1
Color	White (WH)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

[Product Dimensions](#)

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	2.01"
Width (W)	51.05mm
Width (W2)	2.0" / 50.8mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	0.75" / 19.1mm
Width (W6)	0.5" / 12.7mm
Height (H)	1.05" / 26.7mm
Mounting Hole Centers	4" / 101.6mm

[Material and Specifications](#)

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	UL / CSA
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes / Yes

[Logistic and Packaging](#)

Packaging Type	box
Pkg. Qty.	30 / 9.1
Carton Qty.	120
UPC	089306295433

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)