




MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

**SWITCH – TOGGLE
ABOVE PANEL MOUNT**

CATALOG LISTING
2TP118 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH



CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON 4		
	LUG SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE LUG (2-3, 5-6)
2TP118-1	ON	OFF	ON
2TP118-2	OFF	NONE	ON
2TP118-3	ON	NONE	ON
2TP118-21	NONE	OFF	ON
2TP118-31	NONE	ON	ON
2TP118-4	MOM OFF	NONE	ON
2TP118-5	MOM ON	OFF	ON
2TP118-6	MOM ON	NONE	OFF
2TP118-7	MOM ON	OFF	MOM ON
2TP118-8	MOM ON	NONE	ON
2TP118-51	NONE	ON	MOM ON
2TP118-61	MOM ON	OFF	NONE

ELECTRICAL DATA	
L191	15A 125, <u>250</u> , 277 VAC 1/2HP 125 VAC 1HP <u>250</u> , 277 VAC 5A 125 VAC "L"
L192	10A 125, <u>250</u> , 277 VAC 1/4HP 125 VAC, 1/2HP <u>250</u> , 277 VAC 3A 125 VAC "L"



- NOTES
1 – SWITCH WILL WITHSTAND TEMPERATURE OF 160°F
2 – MICRO SWITCH CAT. LIST. MARKED ON SIDE OF SWITCH
3 SCREWS FURNISHED UNASSEMBLED
4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .13 LB EST