

The innovative SB® connectors provide cost-effective reliability, design flexibility and safety for your products' manufacture, installation and maintenance.

APP's 2 pole connector is available with a 120 amp rating, 600 Volts continuous AC or DC operation. There are SB® connectors for many applications and wire sizes, #2 to #6 AWG (33.6 to 13.3 mm²). Mechanical keys ensure connectors will only mate with connectors of the same color. Different color housings are selected to identify voltages, thus preventing mismatching of the power supply system.

FEATURES

- **Molded side grooves**

Allows for a secure panel mounting fit

- **Mechanical keyed housings**

Prevents accidental mating of components operating at different voltage levels

- **Single-piece housing and unitized construction**

Provides industrial quality and durability



PRODUCT SPECIFICATIONS

Connector Model	SB ®120	Connector Model	SB ®120
UL Current Rating (Amperes)*	120*	Life	
UL Voltage Ratings (Volts)	600*	a. No load (Contact/Disconnect Cycles)	To 10,000
Contact Barrel Wire Size (AWG)	#2 to #6	b. Under Load (Hot Plug 250 cycles @ 120V)	60A
(mm ²)	33.3 to 13.3	Avg. Connection/Disconnect (lbs)	20
Maximum Wire Insulation Diameter (inches)	0.575	Operating Temperature Range °C**	-20° to 105°
(mm)	14.6	Flammability Rating of Housing Material	UL94 V-0
AVG Contact Resistance*	136		
(micro-ohms)			
Insulation Withstanding	2200		
Test Voltage (Volts AC/DC)			
Contact Retention Force (lbs)	100		

* UL Rated for 75°C rated wire or cable size

** Contact factory for higher temperature rated connector

SB®, UL and CSA Reference: This equipment is an Underwriters Laboratories Inc® recognized component. It is also listed by the Canadian Standards Association as certified.

ORDERING INFORMATION

2 Pole Housing & 120 amp Contacts

Part Number	Housing Color	Wire AWG	Wire sq. mm
6800G1	Gray	#2	33.6
6801G1	Blue	#2	33.6
6802G1	Red	#2	33.6
6800G2	Gray	#4	21.1
6801G2	Blue	#4	21.1
6802G2	Red	#4	21.1
6800G3	Gray	#6	13.3
6801G3	Blue	#6	13.3
6802G3	Red	#6	13.3

Housing Only

Part Number	Description
6810G1	Gray housing
6810G2	Blue housing
6810G3	Red housing

120 amp Contacts

Part Number	Description	Wire AWG	Wire sq. mm
1319-BK	Bulk, low detent	#2	33.6
1319G4-BK	Bulk, low detent	#4	21.2
1319G6-BK	Bulk, low detent	#6	13.3
6811G1	Set (2), low detent	#2	33.6
6811G2	Set (2), low detent	#4	21.1
6811G3	Set (2), low detent	#6	13.3

Bushings

Part Number	Description	Wire AWG	Wire sq. mm
5919	Use with 6811G1 #2 to #4		33.6/21.2
5920	Use with 6811G1 #2 to #6		33.6/13.3
5921	Use with 6811G1 #2 to #8		33.6/8.4

Accessories

Part Number	Description
SB120-HDL-RED	SB handle with hardware-red
981G1	Cable clamp for 2 single conductor cables
1467G1	Panel mounting bracket

Tooling

Part Number	Description
1368	Hand tool - #2 to #8
1387G1	Pneumatic tool - #2 to #8
1388G4	- die for #2 to #8
1389G4	- locator #2 to #8

HEADQUARTERS: 13 Pratts Junction Road, P.O. Box 579, Sterling, MA 01564 T:978-422-3600 F:978-422-3700

EUROPE: Rathealy Road, Fermoy Co. Cork, Ireland T:353-(0)25-32277 F:353-(0)25-32296

ASIA/PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong

T:852-2636-0836 F:852-2635-9036


www.andersonpower.com

DIMENSIONS

Housing


	-A-		-B-		-D-		-E-		-F-	
Series	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
SB®120	19.05	.75	35.81	1.41	44.45	1.75	63.5	2.50	104.65	4.12

	-H-		-J-		-K-		-L-		-M-	
Series	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
SB®120	20.62	.81	5.05	.20	23.37	.92	2.54	.10	1.52	.06




Contacts

Part Number	Contact Detent	-A- mm	-A- in.	-B- mm	-B- in.	-C- mm	-C- in.	-D- mm	-D- in.	-E- mm	-E- in.
1319-BK	Low	50.8	2.00	11.1	.44	8.7	.34	21.6	.85	10.4	.41
1319G4-BK	Low	50.8	2.00	11.1	.44	7.5	.30	21.6	.85	10.4	.41
1319G6-BK	Low	50.8	2.00	11.1	.44	5.6	.22	21.6	.85	10.4	.41
6811G1	Low	50.8	2.00	11.1	.44	8.7	.34	21.6	.85	10.4	.41
6811G2	Low	50.8	2.00	11.1	.44	7.5	.30	21.6	.85	10.4	.41
6811G3	Low	50.8	2.00	11.1	.44	5.6	.22	21.6	.85	10.4	.41





Bushings - (for use with 6811G1 contacts)

Part Number	Reduces From	-A- mm	-A- in.	-B- mm	-B- in.	-C- mm	-C- in.
5919	#2 to #4 AWG	21.34	.84	8.36	.329	7.24	.285
5920	#2 to #6 AWG	21.34	.84	8.36	.329	5.76	.227
5921	#2 to #8 AWG	21.34	.84	8.36	.329	4.6	.181



TEMPERATURE RISE CHARTS



CSA Certified
File No. LR25154



UL Recognized
File No. E26226

All Data Subject To Change Without Notice

DS-SB120 REV04

HEADQUARTERS: 13 Pratts Junction Road, P.O. Box 579, Sterling, MA 01564 T:978-422-3600 F:978-422-3700

EUROPE: Rathealy Road, Fermoy Co. Cork, Ireland T:353-(0)25-32277 F:353-(0)25-32296

ASIA/PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong

T:852-2636-0836 F:852-2635-9036

www.andersonpower.com