

ELECTRONIC BUZZER



ROHS COMPLIANT UPON REQUEST

PART NUMBER:

BS2316P-24-C

SPECIFICATIONS:

RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	16 ~ 27 VD
MAX CURRENT:	35 mA
SOUND OUTPUT LEVEL:	80 dB @ 30
TERMINAL TYPE:	4 PINS
RESONANT FREQUENCY:	400 ± 50 H
OPERATING TEMPERATURE:	-40 TO + 70°C
FRAME DIAMETER:	23.0 x 17.0 mm
FRAME DEPTH:	15.8 mm
MOUNTING DIMENSIONS:	15.24 x 7.62 mm

DIMENSIONS:

