



 Deutsche Version

[Home](#)

[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

☐ PRODUCTS
ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NEUTRIK



Audio

Phono (RCA)

[back](#)

NYS373-*

Product

Connector Type	Jack
Gender	female

Electrical

Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A

Mechanical

Cable O.D.	≤ 6 mm
Insertion force	≤ 20 N
Withdrawal force	> 5 N
Lifetime	> 1000 mating cycles
Wire size	24 AWG

Material

Bushing	PVC
Contact plating	0.2 µm Au
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1) Black
Strain relief	Internal plastic chuck

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C