


Part Number: 736

Type	Size	Rating	Description
Incandescent	T6	28V 40mA	T-1¾ Midget Flange Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	40	44	48	3.5	4.0	4.5	10,000

Notes:

- Base Type** Nickel plated brass shell SX6s base to BS EN 60061-1 (sheet 7004-61-1)
- Filament Shape** C-2F
- Lamp Marking** CML736 28V 40mA engraved or ink stamped on base shell
- Environmental** RoHS & REACH SVHC compliant