

## PA56TS48DD-WO

SPANSION S29GL512M

| TSOP56 |         | DIP48 | DIP48 | TSOP56   |    |
|--------|---------|-------|-------|----------|----|
| 3      | A15     | 1     | 48    | A16      | 54 |
| 4      | A14     | 2     | 47    | A24      | 56 |
| 5      | A13     | 3     | 46    | A22      | 2  |
| 6      | A12     | 4     | 45    | DQ15/A-1 | 51 |
| 7      | A11     | 5     | 44    | DQ7      | 50 |
| 8      | A10     | 6     | 43    | DQ14     | 49 |
| 9      | A9      | 7     | 42    | DQ6      | 48 |
| 10     | A8      | 8     | 41    | DQ13     | 47 |
| 11     | A19     | 9     | 40    | DQ5      | 46 |
| 12     | A20     | 10    | 39    | DQ12     | 45 |
| 13     | WE#     | 11    | 38    | DQ4      | 44 |
| 14     | RESET#  | 12    | 37    | * Note 2 |    |
| 15     | A21     | 13    | 36    | DQ11     | 42 |
| 16     | WP#/ACC | 14    | 35    | DQ3      | 41 |
| 1      | A23     | 15    | 34    | DQ10     | 40 |
| 18     | A18     | 16    | 33    | DQ2      | 39 |
| 19     | A17     | 17    | 32    | DQ9      | 38 |
| 20     | A7      | 18    | 31    | DQ1      | 37 |
| 21     | A6      | 19    | 30    | DQ8      | 36 |
| 22     | A5      | 20    | 29    | DQ0      | 35 |
| 23     | A4      | 21    | 28    | OE#      | 34 |
| 24     | A3      | 22    | 27    | * Note 1 |    |
| 25     | A2      | 23    | 26    | CE#      | 32 |
| 26     | A1      | 24    | 25    | A0       | 31 |

|                                                  |  |
|--------------------------------------------------|--|
| * Note 1 (GND)                                   |  |
| DIP48 - 27                                       |  |
| TSOP56 - 33(Vss), 52(Vss)                        |  |
| * Note 2 (VCC)                                   |  |
| DIP48 - 37                                       |  |
| TSOP56 - 17(RY/BY#), 43(Vcc), 29(Vio), 53(BYTE#) |  |

## PA56TS48DD-WO PartList

SPANSION S29GL512M

|    |            |   |                                 |
|----|------------|---|---------------------------------|
| 1. | TOP Board  | : | PA56TS48DB_C_D-WO-TOP<br>REV2.0 |
|    | BOT Board  | : | 48 DIP TYPE A                   |
|    | Socket P/N | : | 648-0562211-A01                 |
|    | C1         | : | 0.1uF                           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EETools:](#)

[PA56TS48DD](#)