


LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
G		14								J		REV,RDRW,& SM PKG PER 0720-0061-93		4-16-93		JAD	

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

- 1 STAMP AMP 12-10 APPROX AS SHOWN
- 2 WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL



50	LOOSE PIECE, BOX	8-323683-2
2500	ON TAPE	2-323683-2
---	LOOSE PIECE	323683
QUANTITY	PACKAGING TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 649°C MAX	VOLTAGE RATING: NOT APPLICABLE	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS SOLID OR STRANDED
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 4-16-93 TA BRINKMAN CHK 4-16-93 DA PATTERSON APPD 4-16-93 DE MILLER APPD 4-16-93 JL MECKLEY PRODUCT SPEC -
MATERIAL NICKEL PER ASTM B-162 ANNEALED	FINISH -

DR 4-16-93 TA BRINKMAN	CHK 4-16-93 DA PATTERSON	APPD 4-16-93 DE MILLER	APPD 4-16-93 JL MECKLEY	PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -
---------------------------	-----------------------------	---------------------------	----------------------------	-------------------	-----------------------	-------------

AMP AMP Incorporated Harrisburg, PA 17105-3608		NAME TERMINAL, RING TONGUE, HIGH TEMPERATURE, STRATO-THERM™	
SIZE C	CAGE CODE 00779	DRAWING NO C=323683	
SCALE 8:1		SHEET 1 OF 1	