

## G-type Twin Wheel Caster




### Characteristic

Small turning radius with its twin wheels.

### Application


Large size office automation appliances, etc.

#### G7N□S (with stopper)



| Model No. | Material |       | Allowable Load (kg) | Net Weight (g) | Code No. |
|-----------|----------|-------|---------------------|----------------|----------|
|           | Body     | Wheel |                     |                |          |
| G7        | ADC      | PA    | 150                 | 250            | 9924     |
| G7S       |          |       |                     | 264            | 9928     |
| G7N3      |          |       |                     | 178            | 9925     |
| G7N3S     |          |       |                     | 192            | 9929     |
| G7N10     |          |       |                     | 178            | 9926     |
| G7N10S    |          |       |                     | 192            | 9930     |
| G7N12     |          |       |                     | 188            | 9927     |
| G7N12S    |          |       |                     | 202            | 9931     |

#### G7S (with stopper)



### Size List

| Model No. | A  | B   | C   | D   | E  | G    | d    | H1   | H2 | J1   | J2 | K  | L  | W1 | W2 |
|-----------|----|-----|-----|-----|----|------|------|------|----|------|----|----|----|----|----|
| G7        | 55 | φ48 | φ62 | φ60 | 17 | φ6.5 | W3/8 | 79.5 | 70 | t3.8 | t6 | 17 | 19 | 44 | 18 |
| G7S       |    |     |     |     |    |      |      |      |    |      |    |    |    |    |    |
| G7N3      |    |     |     |     |    |      |      |      |    |      |    |    |    |    |    |
| G7N3S     |    |     |     |     |    |      |      |      |    |      |    |    |    |    |    |
| G7N10     | 55 | φ48 | φ62 | φ60 | 17 | φ6.5 | M10  | 79.5 | 70 | t3.8 | t6 | 17 | 19 | 44 | 18 |
| G7N10S    |    |     |     |     |    |      |      |      |    |      |    |    |    |    |    |
| G7N12     |    |     |     |     |    |      |      |      |    |      |    |    |    |    |    |
| G7N12S    | 55 | φ48 | φ62 | φ60 | 17 | φ6.5 | M12  | 79.5 | 70 | t3.8 | t6 | 17 | 22 | 44 | 18 |

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.