







NOTES:
MATERIAL:
CONTACTS:BRASS T=0.25mm
INSULATOR:PBT+30%G.F. UL 94V-0
FRONT SHELL:BRASS T=0.30mm
BACK SHELL:SPCC T=0.30mm
SPRING:SPCC
MECHANICAL:
MATING:35N MA
WITHDRAWAL FORCE:10N MIN
DURABILITY:1500CYCLES MIN
ELECTRICAL:
CURRENT RATING1.5A
VOLTAGE RATING:30V
WITHSTANDING VOLTAGE:750V AC
CONTACT RESISTANCE:25mΩ MAX
INSULATION RESISTANCE:1000MΩ MIN
PLATING
CONTACTS:GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL:NICKEL OVER ALL PLATING
ENVIRONMENTAL:
TEMPERATURE RANGE:-55°C TO+85°C



P.C.B LAYOUT

10/01/30	ING	EG-N1012072			A3
09/12/29	BENDEE	EG-H12067	變更尺寸標注位置		A2
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表			CnC Tech,LLC		
X.X ±0.38					TITLE: USB 8P A/F 雙層DIP 90°雙彈片5U"成品
X.XX ±0.25			APPD:		PRODUCT NO: 1001-004-01010
X.XXX ±0.13			CHECK:		DATE
			DRAW:		SCALE
					UNIT
					TYPE
					PAGE
					1 / 1