


Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-313	T-3¼	BA9s	28V .17A	C-2F

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max	
28	.153	.170	.187	2.80	3.50	4.20	500 Hrs

Dimensional Characteristics:

1. L.C.L = .63" (16mm)
2. Base = Nickel-plated Brass Construction
3. ANSI Standard. No. 313
4. Part Mark: WL-313



RoHS Compliant

			Title: T-3¼ Miniature Bayonet Base Lamp 28V .170A Vacuum	
Revised	01/24/12	EB	Notes: Unless otherwise specified, all dimensions are in mm.	Rev: 1
Drawn	06/22/00	SL		
Checked	06/22/00	EB		
Approved	06/22/00	EB		