

# 80W high power LED Flood fixture

## Features:

45 Mil Epistar chip  
 Beam Angle: 60 ° /140 °  
 CE, RoHS, LVD, FCC, IP65 Certification






## Specifications:

Commodity	80W high power led flood fixture
Input Voltage	AC85-265V
Frequency Range	50~60Hz
Power Factor (PF)	>0.9
Lamp's Efficiency (%)	> 90%
Colour	White
Colour Temperature	2700-3500K/6000-6500K
Power	80W
Lumens	6400-7200LM
Type of LED	Epistar
Beam Angle	120°-140°/60°
Color Index(CRI)	Ra > 80
Working Temperature	(-30 °C) ~ (45 °C)



## Dimensions:



## Applications:

The led projector is used for billboards, squares, buildings, theatres, parks, gardens, ect.

