

Soldering Stations from **ANTEX**

ANALOGUE



660A

DIGITAL



690D


HOT AIR - REWORK



760RWK

- Stations include power supply, New* ST6a iron stand and a lightweight 50W industrial grade soldering iron fitted with silicone heat-resistant cable and a 2.3mm (1100) bit
- Temperature range continually adjustable from 200°C to 450°C
- LEDs indicate mains power and iron power
- Housed in a robust metal enclosure, which is suitable for the most demanding industrial and educational environments
- Replacement bits and soldering irons are available separately
- Fully compatible with the latest European EMC and CE regulations
- Supply voltage - 230V AC
- Iron voltage - 24V
- Power - 50 Watts
- Leakage current <2.0μA

RANGE OF TIPS

1100		2.3mm
1101		3.0mm
1102		4.7mm
1103		6.0mm
1105		0.5mm
1106		1.0mm
1107		0.12mm
1108		3.0mm
1109		5.0mm



ANALOGUE



SPECIFICATION - IRON / STATION

Max Power 60W
Temperature Range 200 - 450°C
Temperature Stability $\pm 2^\circ\text{C}$ No load
Input Voltage / frequency 230V / 50Hz
Output Voltage 24V
Temp rise time (20-350°C) 55 seconds
Weight 2.5Kg
Dimensions 160x95x141mm

FEATURES

Analogue temperature control
Suitable for lead free soldering
Full range of spare tips available
Sensor close to tip for fast temperature feedback
Digital temperature calibration

INCLUDED IN THE SET

Controller
TC50A soldering iron
ST6a soldering iron stand

DIGITAL



SPECIFICATION - IRON / STATION

Max Power 60W
Temperature Range 200 - 450°C
Temperature Stability $\pm 2^\circ\text{C}$ No load
Input Voltage / frequency 230V / 50Hz
Output Voltage 24V
Temp rise time (20-350°C) 55 seconds
Weight 2.5Kg
Dimensions 160x95x141mm

FEATURES

Digital temperature control
Suitable for lead free soldering
Full range of spare tips available
Sensor close to tip for fast temperature feedback
Digital temperature calibration

INCLUDED IN THE SET

Controller
TC50A soldering iron
ST6a soldering iron stand

HOT AIR - REWORK

SPECIFICATION - IRON / STATION

Max Power 60W
Temperature Range 200 - 450°C
Temperature Stability $\pm 2^\circ\text{C}$ No load
Input Voltage / frequency 230V / 50Hz
Output Voltage 24V
Temp rise time (20-350°C)
Weight 2.75Kg
Dimensions 160x95x141mm

SPECIFICATION - HOT AIR REWORK TOOL

Max Power 700W
Temperature Range 100 - 500°C
Handle size 240mm
Handle weight 180g

FEATURES

Digital temperature control
Suitable for lead free soldering
Full range of spare tips available
Sensor close to tip for fast temperature feedback
Digital temperature calibration

INCLUDED IN THE SET

Controller
TC50A soldering iron
ST6a soldering iron stand
Hot air rework tool
2 x hot air nozzles

