

SURGE PROTECTORS

SURGE POWER CENTER & BLOCKS

Electrical Ratings: 125V/15A/1875W
Response Time: ≤ 1 nanosecond
Line Protection: H-N, N-G, H-G
Max Surge Voltage: 6000V
EMI Filtering:

64-0811

100 KHz-50MHz, up to 58 dB

64-0813

100 KHz-100MHz, up to 52 dB



Fig. 1

USE FOR
COMPUTER



Fig. 2

USE FOR
HOME/OFFICE



Fig. 3

USE FOR
HOME/OFFICE



Fig. 4

USE FOR
SHOP/INDUSTRIAL

Retail Part No.	Figure Number	Number Of Outlets	Description	Color	D-DSS Coax Tele	Max Diss in Joules	Max Surge Voltage	Max Spike Current	Clamping Voltage	EMI/RF Filtering	Agency Listing
64-6651	1	5	Metal Power Center	Ivory	T-40 J	260 J	6000 V	4500 amps	330 V	Y	UL

Retail Part No.	Figure Number	Number Of Outlets	Description	Color	15 amp Breaker	D-DSS Coax Tele	Max Diss in Joules	Max Spike Current	Clamping Voltage	Line EMI/RFI Filtering	Protection (mov)	Agency Listing
64-811	3	1	Surge Block	Gray	N	None	270 J	4500 amps	330 V	N	H-N, N-G, H-G	UL
64-813	2	3	Surge Block w/ EMI/RFI Filter	Gray	N	None	171 J	9000 amps	340 V	Y	H-N, N-G, H-G	UL, CSA
64-671	4	8	Industrial Power Block	Yellow Black	Y	None	N/A	N/A	N/A	N/A	N/A	N/A