

Search Results

Evaluate

- Brochures
- PDF-Physical Inf ...
- PDF-Gestion de l ...
- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-PVQ-RD Produ
- Part Drawings
- PDF-PV12PN - Net ...

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

**Text Search: 'PV12PN'**

Your search criteria matched only one product, shown below

**PV12PN**



- Outlets align with rack units allows for optimization and standardization of equipment power cord lengths; reduces cord slack and congestion behind the equipment, which enhances thermal management
- Six 30A power outlet units can be mounted on one side of the Net-Access™ Cabinet providing 90 Amps redundant power in the space of 2 traditional 66" vertical power outlet units
- Monitor key power criteria via the network or local LED display on unit
- (2) 15 amp magnetic breakers to protect equipment and power infrastructure
- Tool-less mounting
- Slots adjacent to outlets accommodate Panduit's plug retention device (part number PRPC13-60 for black and -69 for ivory) to ensure a secure connection and provide outlet labeling location

• Part Number	PV12PN
• RoHS Compliancy Status	Compliant
• Part Description	Vertical networked power outlet unit 30 Amp, 240V, twelve IEC C-13 receptacles, two 15 Amp magnetic breakers, red LED scrolling monitor, 10' power cord with IEC 309 plug. CE TUV T-Mark
	Dimensions: 24.12"H x 1.75"W x 7.0"D (613mm x 44.5mm x 178mm)
• Color	Black
• Pricing Description	Cabinet Net-Access Power Strip Vertical 12-C13 outlets with Two Pin plug, Metered and Networked
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.