



	1	2	3	4	5	6	7																																																												
A								A																																																											
B								B																																																											
C								C																																																											
D		<table><tr><th>WSW P/N</th><th>Length</th><th>⑨ PE BAG</th><th>⑩ PE BAG</th></tr><tr><td>AK243-2</td><td>2000±30</td><td>130*230*0.05mm</td><td>280*330*0.05mm</td></tr><tr><td>AK243-10</td><td>10000±100</td><td>210*250*0.05mm</td><td>360*380*0.05mm</td></tr><tr><td>AK243-015</td><td>1500±50</td><td>130*230*0.05mm</td><td>280*330*0.05mm</td></tr><tr><td>AK243-025</td><td>2500±50</td><td>130*230*0.05mm</td><td>280*330*0.05mm</td></tr><tr><td>AK243-050</td><td>5000±50</td><td>150*280*0.05mm</td><td>280*330*0.05mm</td></tr></table>					WSW P/N	Length	⑨ PE BAG	⑩ PE BAG	AK243-2	2000±30	130*230*0.05mm	280*330*0.05mm	AK243-10	10000±100	210*250*0.05mm	360*380*0.05mm	AK243-015	1500±50	130*230*0.05mm	280*330*0.05mm	AK243-025	2500±50	130*230*0.05mm	280*330*0.05mm	AK243-050	5000±50	150*280*0.05mm	280*330*0.05mm	Electrical test: 1.100% short,open,miswire test 2.Conduct resistance:5 Ohm(max) 3.Insulation resistance:5Mohm(min) 4.dielectric test:DC 300V	D																																			
WSW P/N	Length	⑨ PE BAG	⑩ PE BAG																																																																
AK243-2	2000±30	130*230*0.05mm	280*330*0.05mm																																																																
AK243-10	10000±100	210*250*0.05mm	360*380*0.05mm																																																																
AK243-015	1500±50	130*230*0.05mm	280*330*0.05mm																																																																
AK243-025	2500±50	130*230*0.05mm	280*330*0.05mm																																																																
AK243-050	5000±50	150*280*0.05mm	280*330*0.05mm																																																																
E	<table><tr><td>⑪</td><td>TIE</td><td>2</td><td>BLACK</td></tr><tr><td>⑩</td><td>PE BAG</td><td>1/10</td><td>CLEAR PRINT BLACK"MADE IN CHINA"+"10PCS"</td></tr><tr><td>⑨</td><td>PE BAG</td><td>1</td><td>CLEAR PRINT BLACK"MADE IN CHINA"+"1PC"</td></tr><tr><td>⑧</td><td>TUBE</td><td>3</td><td>HEAT SHRINK TUBE BLACK OD1.5*10mm</td></tr><tr><td>⑦</td><td>S/R</td><td>1.5g</td><td>BLACK PVC 40P (Mould NO.:SR-048)</td></tr><tr><td>⑥</td><td>IN JACKET</td><td>0.8g</td><td>CLEAR LD-PE (Mould NO.:NM-006)</td></tr><tr><td></td><td>OUT JACKET</td><td>3.3g</td><td>PVC-40P RED(RD-35).(Mould NO.WM-009)</td></tr><tr><td>⑤</td><td>IN JACKET</td><td>0.8g</td><td>CLEAR LD-PE (Mould NO.:NM-006)</td></tr><tr><td></td><td>OUT JACKET</td><td>3.3g</td><td>PVC-40P WHITE(W-100)(Mould NO.WM-009)</td></tr><tr><td>④</td><td>OUT JACKET</td><td>3.0g</td><td>BLACK PVC-40P (Mould NO.:WM-020)</td></tr><tr><td>③</td><td>CABLE</td><td>1</td><td>NOUL [(10/0.10)+S(28/0.10)]*2F JACKET BLACK OD2.8*5.6mm</td></tr><tr><td>②</td><td>CONN</td><td>2</td><td>RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN</td></tr><tr><td>①</td><td>CONN</td><td>1</td><td>3.5ST MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK</td></tr><tr><td>NO.</td><td>NAME</td><td>Q'TY</td><td>SPECIFICATION</td></tr></table>							⑪	TIE	2	BLACK	⑩	PE BAG	1/10	CLEAR PRINT BLACK"MADE IN CHINA"+"10PCS"	⑨	PE BAG	1	CLEAR PRINT BLACK"MADE IN CHINA"+"1PC"	⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm	⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)	⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)		OUT JACKET	3.3g	PVC-40P RED(RD-35).(Mould NO.WM-009)	⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)		OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.WM-009)	④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)	③	CABLE	1	NOUL [(10/0.10)+S(28/0.10)]*2F JACKET BLACK OD2.8*5.6mm	②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN	①	CONN	1	3.5ST MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK	NO.	NAME	Q'TY	SPECIFICATION	E			
⑪	TIE	2	BLACK																																																																
⑩	PE BAG	1/10	CLEAR PRINT BLACK"MADE IN CHINA"+"10PCS"																																																																
⑨	PE BAG	1	CLEAR PRINT BLACK"MADE IN CHINA"+"1PC"																																																																
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm																																																																
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)																																																																
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)																																																																
	OUT JACKET	3.3g	PVC-40P RED(RD-35).(Mould NO.WM-009)																																																																
⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)																																																																
	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.WM-009)																																																																
④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)																																																																
③	CABLE	1	NOUL [(10/0.10)+S(28/0.10)]*2F JACKET BLACK OD2.8*5.6mm																																																																
②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN																																																																
①	CONN	1	3.5ST MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK																																																																
NO.	NAME	Q'TY	SPECIFICATION																																																																
F								F																																																											
G	RoHS compliant Unit: mm <table><tr><th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th>Date</th><th>Name</th><th>Customer-No.</th></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td>Drawn</td><td>20.02.2017</td><td>Amy</td><td rowspan="3">ASSMANN WSW-No. AK243-xx</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>06.01.2020</td><td>Segal</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>①</td><td>Update the SR</td><td>06.01.2020</td><td>Segal</td><td colspan="2" rowspan="2"></td><td>Drawing-No.</td></tr><tr><td></td><td></td><td>②</td><td>Drawn</td><td>20.02.2017</td><td>Amy</td><td>ASS 7856 CA</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Replace</td><td>Sheet</td><td></td></tr></table>							Scale	Free					Date	Name	Customer-No.	TOLERANCE					Drawn	20.02.2017	Amy	ASSMANN WSW-No. AK243-xx						Approved	06.01.2020	Segal									DIM	TOL	①	Update the SR	06.01.2020	Segal			Drawing-No.			②	Drawn	20.02.2017	Amy	ASS 7856 CA	Angle	TOL	Id.	Modification	Date	Name	Replace	Sheet		G
Scale	Free					Date	Name	Customer-No.																																																											
TOLERANCE					Drawn	20.02.2017	Amy	ASSMANN WSW-No. AK243-xx																																																											
					Approved	06.01.2020	Segal																																																												
DIM	TOL	①	Update the SR	06.01.2020	Segal			Drawing-No.																																																											
		②	Drawn	20.02.2017	Amy			ASS 7856 CA																																																											
Angle	TOL	Id.	Modification	Date	Name	Replace	Sheet																																																												
H								H																																																											