




K050DPX/K050DSX 0.5mm Board to Board

Feature

- Mating Height as low as 1.5mm - 6.5mm
- Allows for more cost-efficient and space-saving solutions
- Used in digital cameras, mobile phones, and MP3 players.
- Surface mount plug and socket
- Circuit sizes range from 10-120

Performance Specifications

Materials and Finish

Insulator :High Temp. Plastic (UL94V-0)

Contact : Phosphor Bronze

Plating : Gold Plated

Electrical Characteristics

Current rating : 0.5Amps

Voltage rating : 50V AC/DC

Contact resistance : 30m ohm.max.

Insulation resistance : 100M ohm.

Withstanding voltage : 100V AC for one minute

Temperature range : -20°C to +105°C

0.5mm Board to Board Plug

K050DPX/DSX Series

Documentation & Ordering Information

Stock	CofC
Sample	RFQ

Mating Kycon Part Number

Plug	K050DPX-010-120-GT	Drawing
Socket	K050DSX-010-126-GT	Drawing

Part Number Builder

K050DPX	-	010	120	G	-	T
Series		No of Contacts	Height	Plating		Packaging Option

Series

K050DPX - 0.5mm B2B Plug

K050DSX - 0.5mm B2B Socket

Number of Contact

10, 12, 14, 16, 18, 20, 22, 24, 28, 30, 32, 36, 40, 50, 60

Mating Height (mm)

	K050DPX-XXX-120-G (Plug Height)				
	120	170	220	270	320
K050DSX-XXX-126-G	1.5				
K050DSX-XXX-170-G		2.5			
K050DSX-XXX-176-G	2.0				
K050DSX-XXX-220-G			3.0	3.5	
K050DSX-XXX-270-G				4.0	4.5
K050DSX-XXX-420-G			5.0	5.5	
K050DSX-XXX-470-G				6.0	6.5

Plating


G - Gold

Packaging Option



Blank - Tube

T - Tape and Reel Packaging

K050DSX Series



K050DPX Series



Plug or Socket PCB Layout