




RECOMMENDED P. C. B. PATTERN LAYOUT

- 1.MATERIAL:
CONTACTS:PHOSPHOR BRONZE
INSULATOR:LCP+30% G.F. UL 94V-0
SHELL:BRASS
- 2.MECHANICAL:
MATING:35N MAX.
WITHDRAWAL FORCE:10N MIN
DURABILITY:1500 CYCLES MIN
- 3.ELECTRICAL:
CURRENT-MAX[AMPS] 1.5A
VOLTAGE-MAX[VOLTS] 30V
WITHSTANDING VOLTAGE 500V AC
CONTACT RESISTANCE[OHMS] 30milliohms max
INSULATION RESISTANCE [OHMS] 1000 MEGOHMS MIN
- 4.PLATING:
CONTACTS: GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL:NICKEL OVER ALL PLATING
- 5.ENVIRONMENTAL
TEMPERATURE RANGE:-55°C+50°C

09/12/17	ING		NEW DWG				A1		
DATE	DR.BY	ECN.NO.	DESCRIPTION			MARK	VER.		
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表			CnC Tech,LLC						
					TITLE: USB 4P A/F SMT 5U"成品				
X.X	±0.38	X.X° ±2°	APPD:		PRODUCT NO: 1002-002-01100				
X.XX	±0.25	X.XX° ±1°	CHECK:		DATE	SCALE	UNIT	TYPE	PAGE
X.XXX	±0.13	X.XXX° ±0.5°	DRAW:		2009.12.17	1:1	mm	Z	1 / 1