







-
- Figure 1: Pin 1 location on the connector. The diagram shows a 40-pin connector layout. Pin 1 is located at the top right. Dimensions are provided for the pin positions. A note indicates the diameter of the connector is 0.054 ± 0.002 . A note also indicates the diameter of the pin is $0.010 (M)$.



5	OBSOLETE	YES	1-10, 13-29, 29-37	3	1-796125-3
		YES	1-10, 13-29, 29-37	3	1-796125-1
5	OBSOLETE	YES	1-10, 13-29, 29-37	2	796125-3
		YES	1-10, 13-29, 29-37	2	796125-1
		PERIPHERAL SEAL	SELECT LOAD IN POSITIONS	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 22MAY2003 CHK S. HEADER 22MAY2003 APP'D S. HEADER 22MAY2003	 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 23-37, CPC -
		0 PLC ±.0 1 PLC ±0.0 2 PLC ±0.00 3 PLC ±0.000 4 PLC ±0.010 ANGLES ±.		
MATERIAL -		FINISH -		
WEIGHT -		CUSTOMER DRAWING -		
		SIZE A1		CAGE CODE 00779
		DRAWING NO C-796125		RESTRICTED TO -
		SCALE 3:1		SHEET 1 OF 1
		REV G		

RECOMMENDED PANEL CUTOUT
.125 MAX PANEL THICKNESS