

Standard Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to Right Angle IEC-320-C13) 2-ft.

MODEL NUMBER: **P004-002-13RA**



Highlights

- UL Listed
- C13 Right Angle - C14
- 18AWG (0.824mm), SJT, 10A, 100-250V

Package Includes

- 2-ft. universal AC power extension PC style male (IEC-320-C14) to PC style female (IEC-320-C13) Right Angle

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 2ft. cord can be used to extend the power cord on any PC or device with a C14 plug. Features an IEC-320-C14 to IEC-320-C13 Right Angle connection. UL listed.

Features

- UL Listed
- 2-ft. power extension cord for your PC or device with a C14 plug
- Plug type: IEC-320-C14 (male), to IEC-320-C13 (female) Right Angle
- 18AWG (0.824mm), SJT, 10A, 100-250V

Specifications

OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
UPC ASSIGNMENT	

Unit Carton UPC#	037332156419
PHYSICAL	
Color	Black
Style	Power Cables
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	C13 RIGHT-ANGLE
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Model Number	Description	Qty.
P004-004	4-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-006	6-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-002-5	5-Pack of 2-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
P004-002-13LA	AC Power Extension Cable - C13 Left Angle to C14 - 2'	1
P004-006-2C13	6-ft. AC Power Extension Splitter Cable (C14 to 2 x C13)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/P004-002-13RA>.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#)

[P004-002-13RA](#)