



4

3




2

1


LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION		DATE	APVD
			A1	REVISED PER ECO-11-005301		6APR11	HMR



RECOMMENDED PCB LAYOUT



2 PIN



3 PIN

0.36g	17.50	19.30	20.50	15	1-1734829-5
0.34g	16.25	18.05	19.25	14	1-1734829-4
0.32g	15.00	16.80	18.00	13	1-1734829-3
0.30g	13.75	15.55	16.75	12	1-1734829-2
0.27g	12.50	14.30	15.50	11	1-1734829-1
0.26g	11.25	13.05	14.25	10	1-1734829-0
0.23g	10.00	11.80	13.00	09	1734829-9
0.21g	8.75	10.55	11.75	08	1734829-8
0.19g	7.50	9.30	10.50	07	1734829-7
0.16g	6.25	8.05	9.25	06	1734829-6
0.14g	5.00	6.80	8.00	05	1734829-5
0.12g	3.75	5.55	6.75	04	1734829-4
0.10g	2.50	4.30	5.50	03	1734829-3
0.08g	1.25	3.05	4.25	02	1734829-2
WEIGHT	C	B	A	NO. OF CONTACTS	PART NUMBER

- NOTE:
- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
 - FINISH:
CONTACTS: 2.54μm [100μ"] MIN. MATTE-TIN OVER
1.27μm [50μ"] MIN. NICKEL ON ENTIRE CONTACT.
 - WAVE SOLDER CAPABLE TO 265°C PER **TE Connectivity** TEST SPEC. 109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.38
2 PLC ± 0.25
3 PLC ± 0.15
4 PLC ± -
ANGLES ± -
FINISH

SEE NOTE

DWNH. HUANG31MAY2007
CHK S. HOU31MAY2007
APVD W.J. KE31MAY2007
PRODUCT SPEC
108-57499
QUALIFICATION TEST REPORT
501-57573
WEIGHT SEE TABLE

CUSTOMER DRAWING


TE Connectivity

NAME
1.25MM PITCH, WIRE TO BOARD CONNECTOR
HEADER, R/A, DIP TYPE


SIZEA3CAGE CODE00779DRAWING NOC-1734829RESTRICTED TO—

SCALE—SHEET1 OF 2REV A1

LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



5.95 Kg	2.18 Kg	30	200	6000 PCS	15
5.92 Kg	2.15 Kg	32		6400 PCS	14
5.92 Kg	2.15 Kg	34		6800 PCS	13
5.96 Kg	2.19 Kg	36		7200 PCS	12
5.87 Kg	2.10 Kg	39		7800 PCS	11
5.97 Kg	2.20 Kg	43		8600 PCS	10
5.97 Kg	2.20 Kg	47		9400 PCS	09
5.95 Kg	2.18 Kg	52		10400 PCS	08
5.97 Kg	2.21 Kg	58		11600 PCS	07
5.85 Kg	2.11 Kg	66		13200 PCS	06
5.93 Kg	2.16 Kg	76		15200 PCS	05
5.93 Kg	2.16 Kg	90		18000 PCS	04
5.95 Kg	2.18 Kg	110		22000 PCS	03
5.92 Kg	2.14 Kg	141		28200 PCS	02
GROSS WEIGHT	NET WEIGHT	PCS/TUBE	TUBES /CARTON	QUANTITY	NO. OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. HUANG 31MAY2007		 TE Connectivity			
		CHK S. HOU 31MAY2007					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.J. KE 31MAY2007		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		1.25MM PITCH, WIRE TO BOARD CONNECTOR HEADER, R/A, DIP TYPE	
				—			
				APPLICATION SPEC			
MATERIAL		FINISH		—		SIZE	
—		—		WEIGHT		CAGE CODE	
				—		DRAWING NO	
				A3		00779	
				C=		1734829	
				CUSTOMER DRAWING		SCALE	
						—	
						SHEET	
						2 OF 2	
						REV	
						A1	