




This is a sample photo.

Order symbol PCM 200/100 XG	
EI. number	EAN-code 6418074038357
Sweden Denmark Finland 3421622	
Including Enclosure cover with cover screws, body with mounting screws and gasket.	
Product Properties USA: NEMA Type 1,4,4X and 6, 12 and 13 EURO: IP 66 (EN 60529)	

MNX PCM



Technical Information of Product Group

Standard colour:	RA 7035	Temp. range-in cont. use:	- 40 °C - + 80 °C
Flame resistance:	UL94-5V (UL 746 C 5)	Temp. range-of material:	- 40 °C - + 120 °C

Accessories

Sealing bushing	DP 14553
Cover screw head	MB 14552
Condensation water plug	MB 12189
Mounting screw	KN 3.9x9.5
Ventilation device	MB 10631
Inspection window	L 10
Cover screw	SS 14551H
Mounting plate	MIV 200
Swing door kit	HFP 180
DIN-Rail	MIV 20
DIN-Rail	MIN 15
DIN-Rail	MIN 20
DIN-Rail	MIV 15
Front plate	FP A 200/180
Hinge	TH A