

BU-2323-10-XX-*

(Stackable, Retractable Banana Test Lead 10 AWG)

Coolflex45



Coolflex45 cables get their name from the extremely low temperature rise under high current conditions. Testing under a continuous AC load of 45 Amps resulted in only a 30°F (17°C) temperature rise. Coolflex45 cables were also exposed to overcurrent loads of 70 Amps for fifteen seconds and resulted in only a 14°F (8°C) temperature rise. (Note, all testing was performed by an independent, certified laboratory)

- Stackable, retractable banana plugs fit all standard 4mm banana jacks.
- Clear retractable banana sheath provides electrical protection when cable is not mounted.
- Cable is 10 AWG with a highly flexible silicone jacket. Length is designated in inches by the "XX" in the part number.
- Ratings: 600V, 45 Amps. @ 105°C
- Colors: Designated by "*" in the part number: -0 black, -2 red,
- RoHS Compliant