



MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 91929


SWITCH-TOGGLE FLUSH KEY

CATALOG LISTING **2TP69 SERIES** **CHART 1**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH



CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL RATING
	LUG SIDE (1-2,4-5)	CENTER (1-2,4-5)	OPPOSITE LUG (2-3,5-6)	
2TP69-1	ON	OFF	ON	15A-125,250,277 VAC 1/2HP-125VAC;1HP-250,277VAC CODE 191 5A-120VAC "L"
2TP69-2	OFF	NONE	ON	
2TP69-3	ON	NONE	ON	
2TP69-21	NONE	OFF	ON	
2TP69-31	NONE	ON	ON	
2TP69-4	MOM OFF	NONE	ON	10A-125,250,277 VAC 1/4HP-125VAC,1'2HP-250,277 VAC CODE 192 3A-125VAC "L"
2TP69-5	MOM ON	OFF	ON	
2TP69-6	MOM ON	NONE	OFF	
2TP69-7, -7NB/6/7	MOM ON	OFF	MOM ON	
2TP69-8	MOM ON	NONE	ON	
2TP69-51	NONE	ON	MOM ON	RU CE
2TP69-61	MOM ON	OFF	NONE	



- NOTES**
- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 2 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA8
 - 3 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160° F
 - 4 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
 - 5 - FURNISHED UNASSEMBLED
 - 6 - CENTER BARRIER MAY BE BROKEN ON 2TP69-7 ONLY
 - 7 - PRODUCT SUPPLIED WITHOUT BUTTON WHEN "NB" SUFFIX ADDED TO LISTING IE "2TP69-7NB"

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DIMENSIONS UNLESS OTHERWISE SPECIFIED

NO. PLACES	DES.	TOL.	DES.	TOL.
ONE PLACE	1	±.005	1	±.005
TWO PLACES	2	±.002	2	±.002
THREE PLACES	3	±.001	3	±.001

DESIGN UNITS

IN METRIC

US CUSTOMARY

RAW MATERIAL-COMMERCIAL STANDARD

MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE

PROTECTIVE COATINGS ARE APPLIED

WEIGHT