



REV.	DATE	DESCRIPTION
A	01/10/04	UPDATE DRAWING FORMAT
B	03/27/05	ADD 17.5 HEX DIMENSION
C	04/12/06	MODIFY INTERNAL X-SECTION



- CRIMP NOTES:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
 2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE .7mm
 3. MAX. PANEL THICKNESS= 5.0mm

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND DECIMALS THEREOF. DIMENSIONS ARE GIVEN IN PARENTHESES IN MILLIMETERS. DIMENSIONS ARE FOR CUSTOMER REFERENCE ONLY.			APPROVALS		DATE	PART DESCRIPTION TNC REVERSE BULKHEAD CRIMP JACK (FOR RG-178B/U, 196A/U CABLE)
8	FERRULE	COPPER	NICKEL	1		
7	HEX NUT	BRASS	NICKEL	1	04/12/06	
6	LOCK WASHER	BRASS	NICKEL	1	CHECKED	
5	GASKET	RUBBER	RED	1	ISSUED	PART NO. 122370RP
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	SHEET 1 OF 1	
2	INSULATOR	TEFLON	NATURAL	1		
1	BODY	BRASS	NICKEL	1		
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	DMG. NO. 122370RP.DWG
						REV. C
						SIZE A
						SCALE NA