






3 Conductor Mini Stereo Jack 3.5ø -3


161-073SP

KOBICONN

3 Conductor Mini Stereo Jack 3.5ø - 3



Mounting Hole Dimension



Thickness of mounting board:
t=1.0~1.8
(t=.04~.027)

Part	Material	Finish
Contact D	BSR t=0.3	Ni
Contact B	FAB-EH t=0.25	Au
Contact A	FAB-EH t=0.25	Ni
Body	PA 66	
Metal	BSBM	Au

Dimensions: mm (In.)

SPECIFICATIONS

Dielectric strength	500VAC for one minute
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC

Date Last Revised: 3-21-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300239

161-073SP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-073SP](#)