

- Replacement for PAR16 high voltage 35 W Halogen lamp
- Up to 80% energy saving
- Dimmable
- Lifetime of 35,000 hrs
- Built-in TCS (Temperature Control System)
- For accent lighting; ideal for spotlighting of various objects in shops, museums, restaurants etc.



Order Code 52025

General Data

Lamp Socket GU10
Design Lens

Geometric Data

Length (mm) 58
Diameter (mm) 48.5
Weight (g) 62

Electric Data

Wattage 6.5 W
Voltage 220-240 V
Power Factor ≥ 0.90
Operating Frequency 50/60 Hz

Photometric Data

Luminous Flux (lm) 230
CRI ≥ 80
CCT 2700 K –warm white
Luminous Intensity (cd) 950
Beam Angle (°) 25°
Lifetime 35 000hrs

Equivalent to (W) 35 W





Order Code

52025

Product Description

LED PAR16 GU10 6.5W 2700K WW 230LM DIM Box

Technical Packaging Details

Barcode	023942520252
EAN 128	(02)00023942520252(37)40(91)162
EAN 14	50023942520257
Pack Dimensions (HxWxL)	62 mm x 50 mm x 50 mm
Pack Weight	77 g
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	285 mm x 140 mm x 60 mm
Cartons/Layer	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52025

