


SANYO

Cadnica




Cell Type KR-1500AUL

Specifications


Nominal Capacity		1500mAh
Nominal Voltage		1.2V
Charging Current	Standard	150mA
	Fast	2300mA
Charging Time	Standard	14 to 16Hrs.
	Fast	about 1Hr.
Ambient Temperature	Charge	Standard 0°C to +45°C [+32°F to 113°F] Fast 0°C to +45°C [+32°F to 113°F]
	Discharge	-20°C to +60°C [-4°F to 140°F]
	Storage	-30°C to +50°C [-22°F to 122°F]
Internal Impedance (Av.) (at 50% discharge)		16.0mΩ (at 1000Hz)
Weight		30g/1.06oz
Dimensions(D)×(H) (with tube)		17.0 ⁰ _{-0.5} × 43.0 ⁰ _{-1.2} mm
		0.67 ⁰ _{-0.02} × 1.69 ⁰ _{-0.05} inch

Typical Characteristics


Charge




Discharge (at high rate)




Charge



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

