


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			D1	REV PER ECR 07-015095	25JUN07	JR TM



- 1

STAMP "AMP 12-10*", LOCATION APPROX AS SHOWN.
- 2

TONGUE THICKNESS IS 1.0 ± 0.05
- 3

APPLIES TO EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 4

WIRE INSULATION DIA RANGE 3.8-6.4
- 5

BODY - COPPER PER ASTM B-152
SLEEVE - COPPER PER ASTM B-152
INSULATION - NYLON
- 6


BODY - TIN PL PER ASTM B-545
SLEEVE - TIN PL PER ASTM B-545
INSULATION - COLOR - YELLOW
- 7

105°C MAX OPERATING TEMPERATURE.
- 8

300 VOLT MAX
- 9

2.62-6.64mm² [5,180 - 13,100 CMA]
SOLID OR STRANDED

500	LOOSE PIECE	130491
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 12APR07		 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: mm INCHES		CHK T MICHIELUTTI 12APR07							
		APVD T MICHIELUTTI 12APR07		NAME TERMINAL RING TONGUE, PIDG, WIRE SIZE 12-10 —					
		PRODUCT SPEC —							
MATERIAL 		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT —		A3	00779	C-130491	—		
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 1	REV	D1