

Crimping pliers - CRIMPFOX-TC 4 - 1212113

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Why buy this product

- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Crimping pliers for processing turned contacts
- ✓ The integrated positioning tool ensures that the contacts are perfectly aligned in the die



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 454018
GTIN	4046356454018

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height	68 mm

General

Color	black
Compression	Square crimp
Type of contact	Turned contacts
Designation	Crimping position 1
Min. cross section	0.14 mm ²
Max. cross section	1 mm ²
AWG min	26
AWG max	18

Crimping pliers - CRIMPFOX-TC 4 - 1212113

Technical data

General

Designation	Crimping position 2
Max. cross section	1.5 mm ²
AWG max	16
Designation	Crimping position 3
Max. cross section	2.5 mm ²
AWG max	14
Die station	Crimping position 4
Max. cross section	4 mm ²
AWG max	12
Weight	638 g
Min. cross section	0.14 mm ²
Max. cross section	4 mm ²

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>