


- Square caps
- Different top surfaces: flat, convex or concave
- 14.3 mm x 14.3 mm
- h = 19.1 mm; 20.2 mm; 20.1 mm
- Material: ABS/polycarbonate
- Temp. Range:
 - Solid cap: -40/+65°C
 - Transparent cap: -40/+85°C
- Panel cut-out: 1KS/1KBS/1KCS-14.7 x 14.7


All dimensions in mm




Custom solution

DIMENSIONS


SMD w/LED + 1KS




TH w/LED + 1KBS



SMD w/LED + 1KCS



Bezel (optional)



ILLUMINATED – HOW TO ORDER

Switch	Mounting	Actuation force	LED		Cap		Bezel
5 G	☐ ☐ ☐	☐ ☐	☐ ☐ ☐ ☐	+	☐ ☐ ☐ ☐ 1 1 1 6	+	☐ 2 K ☐ ☐
	TH9 through-hole SH9 surface mount	20 35 65 Q*	01 blue 22 green 42 yellow 61 white 82 red 2242 green/yellow 8222 red/green 8242 red/yellow		Frosted white lens and transparent lid 1KS 1KBS	1KCS	03 grey 06 white 08 red 09 black

*For an illuminated quiet 2.0N switch add Q to the end of the switch part number.

NON-ILLUMINATED – HOW TO ORDER

Switch	Mounting	Actuation force		Cap		Bezel
5 G	☐ ☐ ☐	☐ ☐	+	☐ 1 K S ☐ ☐ 1 6	+	☐ 2 K ☐ ☐
	TH9 through-hole SH9 surface mount	20 20Q 35 65		Frosted white lens 1KS	Colour code 00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black	03 grey 06 white 08 red 09 black

Ordering example:

5GTH93501+1KCS1116+2K09 with illumination OR 5GSH965+1KS09+2K03 without illumination OR *5GTH92082Q (illuminated quiet version)

Please see colour codes, updates of products and changes of specifications on www.mec.dk